


# MAGNIFI

Powerful. Efficient. Intuitive.



The market leader for the last 10 years, Magnifi® software continues to empower NDT inspectors all over the world with innovative and advanced features.

*Cutting-edge electromagnetic acquisition, analysis, and reporting software, Magnifi is a constantly evolving platform boasting powerful data processing tools, multi-technologies support, easy report generation, and an intuitive graphical user interface (GUI).*

## Multi-technology and fully customizable

Introduced in 2011, Magnifi software is used by thousands of operators worldwide for the inspection of a wide range of components. Since its first version, it has integrated several technologies and become even more versatile over time.

Advanced heat exchanger tubing inspections with:

- Eddy Current Technology (ECT) and Eddy Current Array (ECA)
- Near-Field Technology (NFT) and Near-Field Array (NFA)
- Remote-Field Technology (RFT) and remote-field Array (RFA)
- Magnetic Flux Leakage (MFL)
- Internal Rotary Inspection System (IRIS)

Advanced surface inspections with:

- Eddy Current Array (ECA)
- Tangential ECA (TECA)
- Magnetic Flux Leakage Array (MFLA)

Magnifi incorporates several layouts, calibration processes, and display options to tailor parameters for the right tools for each inspection. Truly versatile, Magnifi also enables the import and creation of custom probe setups when required.




## Advanced signal processing

In combination with the industry's highest resolution probes, Magnifi incorporates 2D and 3D C-scans, making analysis more intuitive and results easier to interpret. Up to 256 raw channels can be generated by sequential coil activation and displayed at once in a single C-scan tailored to specific detection needs.

Magnifi makes it possible to use a wide variety of tools to process raw data. Technology-specific tools have also been integrated into the software such as:


- 2D and 3D C-scans
- Real-time filters
- Automatic detection thresholds
- Sizing curves and overlays
- Superimposed channel display
- Customizable info fields
- Subtraction cursor and much more.



## Latest innovations

Magnifi 5 now includes Remote-Field Array (RFA), a new technology and complete probe family dedicated to the inspection of ferrous tubing. The c-scan enables better insight on defect morphology, and the array of sensors increases detection near external features compared to conventional RFT.

The first patent-pending artificial intelligence module aiming at improving efficiency and confidence in final reports is also available in Magnifi 5. This innovation also supports acquisition of higher data quality for ECT inspections.



# FUTUREPROOF FEATURES IN AN EVOLUTIVE PLATFORM


The power, efficiency, and intuition of Magnifi is undeniable

## A thoughtful interface

Magnifi has been designed to facilitate the work of users. Its interface is modern and includes ribbons that group icons in a logical and efficient way. The software is divided into two parts: the Backstage which allows you to adjust more general settings such as preferences and file names, and the Frontstage which is dedicated to data acquisition and analysis.


## Quick setup

Creating your setup can be done with the help of a step-by-step wizard. By selecting the parameters of the component that you have to inspect, the software will automatically recommend the right frequencies and filters and suggest a way to calibrate and build your calibration curves. Surface array probes are also automatically recognized by Magnifi when they are connected to the instrument, helping selecting the right setup and inspection parameters.



## Automatic recording for tubing inspection

Data acquisition and recording can be activated automatically when the probe enters or leaves a tube. This allows the person acquiring the data to avoid having to activate these functions manually on the computer or on the instrument. It is also possible to display the number of tubes being scanned in large print to keep track while away from the screen.



## Keyboard shortcuts

Frequently used functions, from acquisition to analysis, can be performed using keyboard shortcuts. Magnifi 5.0 allows for custom keyboard shortcut configuration, such as entering the desired indication using the selected channel and measurement method.


## Indication detection

The Indications module allows the user to define various zones or even waveform types to trigger a detection threshold. These detection zones can be applied to conventional channels or to C-scans and can be adjusted directly on the Lissajous. For C-scans, when an indication reaches this threshold, it is automatically boxed in and displayed in a list. By clicking on the indication, the cursors are automatically adjusted for a finer signal analysis.

## Create reports in a few simple steps

Many report templates can be selected in Magnifi and linked with the report entries made in the software. Only a few steps are necessary to generate a report with customizable fields, a picture of the component, a list of defects, insightful graphs, and the logo of your company. This makes it simple to provide a final inspection report before leaving the job site.

It makes the reporting even easier by allowing the analyst working on the report to get immediate data access through the cloud.



# INTRODUCING ARTIFICIAL INTELLIGENCE (AI) FOR TUBING INSPECTIONS

The first tool of its kind for ECT tubing inspections

## Artificial Intelligence (AI) in ECT inspections


Using a patent-pending process with AI neural networks, Magnifi automatically detects and positions cursors on tubesheets, support plates, and defects during ECT heat exchanger tubing inspections.

Activated in a few clicks, the AI-ECT module aims to improve confidence in the analysis and support the collection of higher quality data. It is simple to learn and easy to use during both acquisition and analysis.

The AI findings are the suggested potential locations of indications; they are not intended to be an automatic reporting tool. It remains the responsibility of a certified analyst to choose the indications that should be reported.

## Collect Superior Data Quality

With automatic screening during acquisition, AI detection for ECT can instantly validate if the full tube length data was collected.



## Quickly Find Essential Information

Once the AI neural networks have screened the data, two additional tools allow the analyst to quickly find the essential information they want to report.

Tubelist sorting and filtering such as:

- Sort tube in descending order of number of potential indications
- Show only tubes with AI findings
- Show tubes with failed DQV test.


Defect grouping allows the analyst to create groups of indications based on the channel, amplitude range, and phase range. This is especially useful with tubes presenting notable quantities of indications.

## Assisted Analysis for all Tubing Techniques

In addition to AI-based detection, Magnifi offers a complete toolset to automatically detect landmarks and indications for:

- Eddy Current Testing (ECT)
- Remote-Field Testing (RFT)
- Near-Field Testing (NFT)
- Magnetic Flux Leakage (MFL)
- DefHi (ECA)
- Near-Field Array (NFA).

Using a visual representation with detection boxes, the user can easily adjust the detection parameters depending on the tube conditions.



# A NEW LICENSING SYSTEM THAT MAKES YOUR LIFE EASIER

Software licenses are now activated in seconds and can be easily shared within your team



## STD and PRO

The Standard (STD) version of Magnifi desktop supports up to five technologies in conventional modes: ECT, RFT, MFL, NFT, and IRIS. The Professional (PRO) version enables access to advanced inspections with array sensors for ECA, TECA, MFLA, and NFA.

ECT acquisitions are now powered by Artificial Intelligence (AI) modules introduced in Magnifi 5.



## GO and GO AC

Packaged with the latest technology, the Reddy® system combines high portability with an intuitive user experience. For surface inspections with ECA and MFL array, Reddy is driven by Magnifi GO, the embedded version of Magnifi desktop.

For ECT bobbin and AC tubing inspections, the Magnifi GO AC version offers integrated automated acquisition sequences and advanced analysis capabilities for on-the-fly reporting.



## ACQ

During a turnaround, time is of the essence. The Magnifi Acquisition (ACQ) licence supports all required functionalities to maximize collection of high-quality data on heat exchanger tubing inspections with conventional technologies (ECT, RFT, NFT, MFL, and IRIS). ECT acquisitions are now powered by AI modules introduced in Magnifi 5.0. AI detection during acquisition can instantly ensure the entire tube length data collection for improved data quality.



## CPN

Built with the same intuitive interface, Magnifi Companion (CPN) allows desktop analysis of any data acquired with the Reddy unit. Analysts can be up and running in next to no time, with larger data layouts at their fingertips. Whether CPN is used to plan and setup inspections for several instruments or to review field data, operators can take full advantage of Reddy's industry leading capabilities.



## Cloud-based License Key

Maximize utilization and flexibility with Eddyfi Technologies' cloud-based licensing system. Software licenses are now activated in seconds and can be easily shared among your team. Gone are the days when the dongle could get lost, broken, or need to be shipped weeks in advance with the equipment.

# SPECIFICATIONS

GENERAL	ACQ	STD	PRO	GO	GO AC/E	CPN
Control acquisition	•	•	•	•	•	
Reporting capabilities		•	•	•	•	•
Create, load, and save Ectane setup and data files	•	•	•			
Create, load, and save Reddy setup files				•	•	•
Load Reddy Surface ECA and MFL data files			•	•		•
Load Reddy AC data files		•	•		•	•
APPLICATIONS						
ECT inspection for surface and tubing applications	•	•	•	•	•	
Surface inspection with eddy current array (ECA)			•	•		
Surface inspection with TECA Sharck and Sharck HR			•	•		
Surface inspection with MFL array			•	•		
Tubing inspection with RFT, NFT, and MFL	•	•	•			
Tubing inspection with IRIS	•	•	•			
Tubing inspection with array probes (DefHi®, NFA and RFA)			•			
Tubing automated inspection with Probot	•	•	•			
TubePro active link	•	•	•			
CONFIGURATION						
Setup creation wizard and landmarks, sizing curves, and customizable layouts		•	•	•	•	•
Advanced channel processing		•	•			
Software development kit (SDK) availability			•			
Automatic signal detection boxes for conventionnal and array inspection		•	•	•		•
AI-ECT landmark detection engine and full tube-length DQV test for non-ferrous tubing	•	•	•			
AI-ECT defect detection engine for non-ferrous tubing		•	•			
SCAN MODES						
Linear, single axis	•	•	•		•	
Tubing, rotating probes (IRIS)		•	•			
Tubing, single-pass array; tubing, rotating array			•			
Surface, single-pass array and raster scans (single-channel & array probes)			•	•		
VIEWS						
Lissajous (impedance plane), strip chart, information	•	•	•	•	•	•
Voltage plane for RFT	•	•	•			
A-scan for IRIS; projection for IRIS	•	•	•			
2D C-scans			•	•		•
3D C-scans			•			•
VERSION	WINDOWS® COMPATIBILITY			*NOTE		
Magnifi 3.5	Windows 7, Windows 8 and Windows 8.1 (32 and 64-bit editions)			Not tested on Windows 10 nor Windows 11		
Magnifi 4.2 to 4.6	Windows 7, Windows 8 and Windows 8.1 (32 and 64-bit editions)			Not tested on Windows 10 nor Windows 11		
Magnifi 4.7 and 4.8	Windows 8.1 and Windows 10 (32 and 64-bit editions)			Not tested on Windows 11		
Magnifi 5.0 and 5.1	Windows 10 and Windows 11 (64-bit editions)			Unsupported on Windows 8.1 (64-bit). Will not work on Windows 32-bit.		

The information in this document is accurate as of its publication. Actual products may differ from those presented herein.  
 © 2023 Eddyfi Canada, Inc. DefHi, Eddyfi, I-Flex, Magnifi, Sharck, TECA, and their associated logos are trademarks or registered trademarks of Eddyfi Canada, Inc. in the United States and/or other countries. Eddyfi Technologies reserves the right to change product offerings and specifications without notice. Eddyfi Technologies is a Previa Business Unit.

[www.eddyfi.com](http://www.eddyfi.com)

[info@eddyfi.com](mailto:info@eddyfi.com)

